



Part Number : [192130010](#)
Product Description : Avikrimp Wire Pin Terminal
for 22-18 AWG Wire, Mylar Tape Carrier
Series Number : 19213
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : WP-8218T
Packaging Alternative : [192130009](#) (Bag)



Documents and Resources

Drawings

[192130010_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:4ca39064-cffc-40c5-9177-af7a6731f890
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19213
Description	Avikrimp Wire Pin Terminal for 22-18 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 9.40mm
Product Name	Wire Pin,Avikrimp
UPC	800753053502

Agency

CSA	LR18689
UL	E32244

Physical

Flammability	94V-2
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.833/g
Packaging Type	Adhesive Tape on Reel

Plating min - Mating	1.016µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.56mm max.
Wire Size (AWG)	18, 19, 20, 22
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880023</u>
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	<u>638851300</u>

This document was generated on Dec 30, 2025