



Feature Stories



Heavy Duty &
Off-Highway
Vehicles
Emissions
Standards Guides

[Find by Feature](#)
[Browse by Category](#)
[Share](#)

[Search →](#)
[Search Results \(0\)](#)
[Search Options](#)

Select a product type to narrow your search:

Results with your selections: --

[Clear](#)
[Search →](#)

Female Metri-Pack 630 Special Tin Plated Terminal, Cable Insulation Range 3.10 - 2.94 mm Part #12052227

Question about this product?

[Attributes](#)
[Documents \(3\)](#)

Part #:	12052227
Description:	Female Metri-Pack 630 Special Tin Plated Terminal, Cable Insulation Range 3.10 - 2.94 mm
Product Type:	Terminal
Status:	Active
Blade size [mm]:	6.3
Terminal family:	Metri-Pack
Series:	630 SPL
Gender:	Female
Sealed:	Unsealed
Material:	Tin Brass
Plating:	Tin
Minimum Cable Core Cross Section [mm2]:	3.00
Maximum Cable Core Cross Section [mm2]:	3.00
Minimum Cable Diameter [mm]:	2.94
Maximum Cable Diameter [mm]:	3.10
Temperature range [°C]:	-40 to 125