
Part Number : 511120610
Product Description : 2.50mm Pitch Wire-to-Wire Plug Housing, with Optional Panel Mount, 6 Circuits
Series Number : 51112
Status : Obsolete
Product Category : Connector Housings



Documents and Resources

Drawings

511120610_sd.pdf

Specifications

PS-51111-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Obsolete

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	51112
Description	2.50mm Pitch Wire-to-Wire Plug Housing, with Optional Panel Mount, 6 Circuits
Application	Wire-to-Wire
Component Type	Plug
Product Name	N/A
UPC	800754309127

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	1616.800/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.50mm Pitch Wire-to-Wire and Wire-to-Board Receptacle Housings	51111

Use with Part(s)

Description	Part Number
2.50mm and 3.30mm Pitch Male Crimp Terminals	50398

Obsolete

Downloaded from Arrow.com.