Specification Sheet

Part Number: 133-02900



Connector easily installed by pushing into place.

Connection can be released (non-destructive).

Arrowhead locks into place for secure attachment at all times.

Connector Clip with Arrowhead, .15" Panel Thick., 6.1 - 6.6 mm Hole Dia, PA66HIRHS, Gray, 12,000/ctn

Article Number	133-02900
Type	CCAH6.35PT3.8
Color	Gray (GY)
Quantity Per	box
Product Description	HellermannTyton connector clips for rounded holes are mounted by pushing them onto the corresponding clip. The clips provide a wide range of mounting options. The arrowhead locks firmly into place when inserted into the hole and ensures a secure attachment at all times.
Short Description	Connector Clip with Arrowhead, .15" Panel Thick., 6.1 - 6.6 mm Hole Dia, PA66HIRHS, Gray, 12,000/ctn
Global Part Name	CCAH6.35PT3.8-PA66HIRHS-GY

Downloaded from Arrow.com.

Length L (Imperial)	0.48
Length L (Metric)	12.2
Fixation Method	Arrowhead
Width W (Imperial)	0.33
Width W (Metric)	8.4
Height H (Imperial)	0.53
Height H (Metric)	13.46
Panel Thickness Min (Imperial)	0.15
Panel Thickness Max (Imperial)	0.15
Panel Thickness Min (Metric)	3.81
Panel Thickness Max (Metric)	3.81
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.1 - 6.6 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.6

Downloaded from Arrow.com.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	12000
Package Quantity (Metric)	12000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.