

1825910-7 Product Details



1825910-7

TE Internal Number: 1825910-7

[Active](#)

Pushbutton Switches



[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Switch
- Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 50mA
- Operating Function = Off [On]

[View all Features](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Have a Question?

[Chat with a Product Information Specialist](#)



[Chat with a Product Information Specialist](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [6MM TACT SWITCH, THRU-HOLE HIGH TEMP](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Switch
- Tactile = Yes
- Configuration (Pole-Throw) = Single Pole - Single Throw
- Mount Angle = Vertical
- Termination Type = Printed Circuit
- Actuator Style = Round

Electrical Characteristics:

- Contact Rating = 50mA

Body Related Features:

- [Series](#) = FSM
- Mount Style = Through-Hole
- Actuator Length (mm [in]) = 1.40 [0.055]
- Actuator Profile = Extended
- Actuator Color = Red
- Case Material = Nylon
- Actuator Material = PBT

Contact Related Features:

- Contact Plating = Silver

Housing Related Features:

- Process Sealed = No
- Low Profile = No

Configuration Related Features:

- Operating Function = Off [On]
- Ganged = No
- ESD Grounding Terminal = Without
- Actuator Force (g [oz]) = 260.00 [9.178]
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Rating = High

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = Alcoswitch
- Comment = (On) indicates momentary position.

[BOOKMARK](#)

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat with Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage Your Account](#)

Sign up for our eNewsletter



Follow Us On:



Visit Us On:

