Part Number : 351513219
Product Description : VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Yellow, Glow-Wire Capable
Series Number : 35151
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

351513219_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

351500000AS_ENG-000.pdf

351500000AS_KOR-000.pdf

PK-35151-001-001.pdf

PS-35150-001-001.pdf

PS-35150-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35151
Description	VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Yellow, Glow-Wire Capable
Application	Wire-to-Wire
Component Type	Plug
Product Name	VersaBlade
UPC	822350608589

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Yellow
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	No

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	1.593/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	2026500909
VersaBlade Hybrid Receptacles Housings and TPAs	35150
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	35524

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	351500290
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	351500292
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	351500293
VersaBlade Terminal Position Assurance (TPA) Retainer,	351500294

Downloaded from Arrow.com.

6.20mm Pitch, 2 Circuits, Blue	
VersaBlade Female Crimp Terminals	35746

Downloaded from Arrow.com.