

Fast Ethernet Passive 24V @ 500mA Power Over Ethernet Plus (PoE+) Injector

Model: FEPOE



KEY FEATURES

- Fast Ethernet Power over Ethernet (PoE) Injector delivers a PoE signal for distances of up to 100 meters (328 ft.)
- Fast Ethernet speeds
- Supplies power up to 12 Watts
- Universal Input 100 to 240V AC
- RoHS Compliant
- Save on installation and equipment costs

Specifications

Output Voltage	24V DC @ 500mA
Power Consumption	12 Watts
Efficiency	72%
Line Regulation	5%
Load Regulation	5%
MTBF	10,000 hours
Standard	Passive 24V PoE
Network Media	10Mbps: UTP/STP Cat. 5 and 5e up to 100 Meters 100Mbps: UTP/STP Cat. 5, and 5e up to 100 Meters
Ports	1 x 10/100Mbps DATA-IN (Data only) 1 x 10/100Mbps PWR+DATA-OUT
RoHS Compliance	Yes
Environmental	Temperature: Operating: 0°C to 40°C, Storage: -20°C to 50°C Humidity (non-condensing): Operating: 15% to 90%,Storage: Max. 95%
Certification	Pending
Dimension (W x H x D)	84 x 47 x 54 mm

Mechanical Dimensions

