






NOTES:
 1. PARTS TO BE BULK PACKED.
 2. PC TAIL CONTACTS ARE PRESSED INTO CONNECTOR.
 3. ALL DIMENSIONS ARE FOR REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE.



FACE VIEW



WIRE VIEW



RECOMMENDED PANEL CUT-OUT
TOLERANCE ±.003 [0.08]

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	AB	05-09-19	RELEASE PER DOR 14-6281TC	
REV.	INIT.	DATE	DESCRIPTION	
<small>ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF CONXALL CORPORATION. UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.</small>		ORIG. DRAWN BY:	DATE:	
		AB	07-18-14	
		CHECKED BY:		
<small>ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.</small>		APPROVED BY:	TITLE:	
				(2) #12 + (6) #26 SOCKET CONTACTS, PC TAIL
				MULTI-CON-X, WEATHER RESISTANT
				CUSTOMER: STANDARD PRODUCT
SCALE NTS	SIZE B	SHEET 1 OF 1	FILE: SAME AS P/N	
REV. A	REV. B	REV. C	REV. D	

► = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX

CONXALL
601 E. WILDWOOD VILLA PARK, IL 60181

TITLE: PANEL CONNECTOR KIT
(2) #12 + (6) #26 SOCKET CONTACTS, PC TAIL
MULTI-CON-X, WEATHER RESISTANT
CUSTOMER: STANDARD PRODUCT

PART NUMBER: W4B81-8SG-300

REV A