

Part Number : [1300960063](#)

Product Description : Safeway Wire Mesh Grip,
Straight Male, Cable Diameter 20.83-25.40mm
(.820-1.000"), Eye Dimension 1 11/16"

Series Number : 130096

Status : Active

Product Category : Cable Grips

Engineering Part Number : 36554




Documents and Resources

Drawings

[1300960063_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130096
Description	Safeway Wire Mesh Grip, Straight Male, Cable Diameter 20.83-25.40mm (.820-1.000"), Eye Dimension 1 11/16"
Product Name	Safeway
Type	Strain Relief Grip
UPC	78678836554

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	20.83-25.40mm (.820-1.000")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	N/A
Net Weight	24.040/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on May 21, 2026