




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		UPDATE DRAWING	10/8/19	LH/JC



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Brown

Pantone Color: 153C~154C

Electrical:

Voltage rating: 300 V AC/DC

Current rating: 3 Amp AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 100 Mohms Min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15

A = .079 [2.00] x No. of Positions + .063 [1.60]

B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
.X ± .10 Ø.X ± .10	.XX ± .020 Ø.XX ± .015	.XXX ± .015 Ø.XXX ± .010					
APPROVALS					DATE		
DRAWN		SS			4/6/05		
CHECKED			TITLE			.079 [2.00] CRIMP HOUSING LOW PROFILE, POLARIZED	
APPROVED			SIZE X		PART NO. 2CH-B-XX		
			REF: S00099T		SCALE: NTS		
					SHEET 1 OF 1		