



Part Number : 191440003

Series Number : 19144

Product Category : Ring and Spade Terminals

Product Description : InsulKrimp Spade
Tongue Terminal for 18-22 AWG Wire

Status : Active

Engineering Number : AA-235-08X


Documents & Resources

Drawings
Drawing 191440003_sd.pdf

Specifications
Product Specification PS-19902-013-001.pdf
Product Specification PS-19902-009-001.pdf
Product Specification PS-19902-011-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19144
Description	InsulKrimp Spade Tongue Terminal for 18-22 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Family	Solderless Terminals
Product Name	InsulKrimp
Type	Spade
UPC	800753104617

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.664/g
Packaging Type	Bag
Stud Size	8 (M4)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.70mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.35-0.80

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 10-22 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050300</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>

This document was generated on May 08, 2024