


© 2025 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-18-015945	09OCT2018	YC	CW
	B1	ECR-19-019179	30DEC2019	YC	CW
	C	ECR-21-117384	09NOV2021	WQR	CW
	D	ECR-25-237972	16JUN2025	ABS	RB









THE CODING PINS ARE PACKAGED WITH PRODUCT
编码销与产品一起包装出货







NOTES:
1. TECHNICAL CHARACTERISTICS:
   INSULATION MATERIAL: PC
   RATED VOLTAGE: 400V
   RATED CURRENT: 40A
   INSULATION RESISTANCE: >=400MΩ
   RATED IMPULSE VOLTAGE: 6KV
   POLLUTION DEGREE: 3
   MATING CYCLES: 500 CYCLES
   WIRE RANGE: 1-10 mm² (18-8 AWG)
   CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
   (ORDER No. REFER TO DRAWING: T20400X20XX000)

注释:
1. 技术参数:
   绝缘材料: PC
   额定电压: 400V
   额定电流: 40A
   绝缘电阻: >=400MΩ
   额定脉冲电压: 6KV
   污染等级: 3
   插拔次数: 500次
   接线范围: 1-10 mm² (18-8 AWG)
   接线类型: 冷压接
2. 端子需要单独订购.
   (订货号参考图面: T20400X20XX000)

PART NUMBER 产品料号		PART DESCRIPTION 产品描述
T2080022201-000	HQ-002-F	HQ-002 FEMALE INSERT HQ-002 母插

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-
MATERIAL - -	FINISH - -

DWN	YORK CHEN	14JUL2017
CHK	GINO YAO	14JUL2017
APVD	CHRIS WANG	14JUL2017
PRODUCT SPEC	108-137310	
APPLICATION SPEC	114-137310	
WEIGHT	-	

TE Connectivity

NAME HQ-002-F

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-T2080022201000	-

CUSTOMER DRAWING | SCALE 3:2 | SHEET 1 OF 1 | REV D

Downloaded from Arrow.com.