




COPPER AIRCRAFT CABLE MIL-W-5086 SIZE	STUD SIZE	CATALOG NUMBER	O.D. MAX.	B MIN.	C MAX.	K MIN./MAX.	L MAX.	N MAX.	T APPROX.	Y APPROX.	Z MIN.	M MAX.	TOOL INDEX NO.
#8	8-10	YBM8C	.320	.41	.47	.193/.203	1.01	.265	.09	.59	.328	.79	54
	1/4	YBM8C-T2		.47	.53	.262/.282	1.07	.297		.62	.360	.82	
	5/16	YBM8C-T3		.53	.59	.321/.341	1.13	.328		.65	.391	.85	
	3/8	YBM8C-T4		.59	.66	.388/.408	1.19	.359		.68	.422	.88	
	8-10	YBM8C-T18		.41	.47	.193/.203	.91	.265		.59	.219	.66	
#6	8-10	YBM6C-L9	.365	.47	.53	.193/.203	1.09	.265	.09	.64	.360	.87	55
	1/4	YBM6C-L		.47	.53	.262/.282	1.12	.297		.64	.360	.87	
	5/16	YBM6C-L2		.53	.59	.321/.341	1.21	.328		.70	.422	.93	
	3/8	YBM6C-L3		.59	.66	.388/.408	1.24	.359		.70	.422	.93	
#4	8-10	YBM4C-L4	.457	.47	.53	.193/.203	1.18	.265	.09	.69	.360	.96	56
	1/4	YBM4C-L		.47	.53	.262/.282	1.21	.297		.69	.360	.96	
	5/16	YBM4C-L1		.53	.59	.321/.341	1.30	.328		.75	.422	1.02	
	3/8	YBM4C-L2		.59	.66	.388/.408	1.33	.359		.75	.422	1.02	
	1/2	YBM4C-L5		.73	.77	.515/.535	1.44	.423		.78	.421	1.10	
#2	1/4	YBM2C-L1	.532	.59	.66	.262/.282	1.28	.297	.09	.73	.360	1.03	57
	5/16	YBM2C-L2		.59	.66	.321/.341	1.38	.328		.79	.422	1.10	
	3/8	YBM2C-L		.59	.66	.388/.408	1.35	.359		.79	.422	1.10	
	1/2	YBM2C-L5		.73	.77	.515/.535	1.57	.453		.84	.451	1.18	
#1	1/4	YBM1C-L1	.582	.59	.66	.262/.282	1.40	.297	.09	.81	.422	1.15	572
	5/16	YBM1C-L2		.59	.66	.321/.341	1.46	.328		.85	.453	1.18	
	3/8	YBM1C-L		.59	.66	.388/.408	1.53	.359		.88	.485	1.21	
	1/2	YBM1C-L3		.84	.91	.515/.535	1.78	.484		1.00	.610	1.34	
	4-6	YBM25-L7		.66	.72	.142/.152	1.49	.297		.86	.422	1.24	
1/0	1/4	YBM25-L1	.674	.66	.72	.262/.282	1.49	.297	.10	.86	.422	1.24	58
	5/16	YBM25-L2		.66	.72	.321/.341	1.56	.328		.89	.453	1.27	
	3/8	YBM25-L		.66	.72	.388/.408	1.62	.359		.92	.485	1.31	
	1/2	YBM25-L6		.84	.91	.515/.535	1.87	.484		1.05	.610	1.43	
	3/8	YBM25		.91	.97	.388/.408	1.72	.469		.92	.484	1.31	
2/0	1/4	YBM26-L2	.760	.78	.84	.262/.282	1.66	.328	.12	.94	.453	1.37	598
	5/16	YBM26-L1		.78	.84	.321/.341	1.65	.328		.94	.453	1.37	
	3/8	YBM26-L		.78	.84	.388/.408	1.71	.359		.98	.485	1.40	
	1/2	YBM26-L3		.84	.91	.515/.535	1.96	.484		1.10	.610	1.53	

MATERIAL: EXTRUDED COPPER
FINISH: TIN PLATED

14	03-09-92	ADD CAT. NO. YBM25-L7 DO 52279	DGF	KH
REV.	DATE	DESCRIPTION	BY	CHK'D

ONE PIECE EXTRUDED HYLUGS, COPPER (PLAT TYPE)	
CAT NO: YBM-L & YBM-T	SCALE: NONE
DRWEN: H.F.C. 05-17-54	CHECKED: 08-17-54
DESIGN APPVL:	WFO APPVL:
U.S. APPVL:	WFO APPVL: N/A
CAD FILE: N/A	PH. REF: N/A
	REL. REF: N/A
PROJECT:	
DRAWING NO. SD30739	
U.S. ELECTRICAL DIVISION MANCHESTER, NH 03108	
SHEET 1 OF 1	