

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, Black, 1991H x 750W x 1200D mm

AR3350

Overview

Lead time Usually in Stock

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	199.1 cm
Width	75 cm
Depth	120 cm
Net weight	161.36 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	104.8 cm
minimum mounting depth	26.19 cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	1020.6 kg dynamic 1701.0 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	211.8 cm
Package 1 Width	85.1 cm
Package 1 Length	133.4 cm
Package 1 Weight	183.18 kg

Contractual warranty

Warranty	5 year repair or replace
-----------------	--------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	556
---	-----

Use Better

Materials and Substances

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

REACH Regulation	REACH Declaration
------------------	-----------------------------------

China RoHS Regulation	China RoHS declaration
-----------------------	--

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
---------------------	---

Take-back	Yes
-----------	-----