

7-1971876-7 Product Details

 Share

 Print

 Email



 Active

 View 3D PDF

Power Triple Lock Connector System

3x5 plug housing Key C lgr

7-1971876-7 

TE Internal Number: 7-1971876-7

Product Highlights [View All](#)

- Power Triple Lock Product Line
- Wire-to-Wire
- Applies To Wire/Cable
- Connector
- Connector Assembly

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features	
Product Line	Power Triple Lock
Product Type	Connector
Connector Type	Connector Assembly

Mechanical Attachment	
Mating Retention Type	Latch(ing)

Electrical Characteristics	
Operating Voltage (VAC)	600
Operating Voltage (VDC)	600

Body Features	
Mating Retention	With
Row-to-Row Spacing (mm [in])	8.10 [0.319]

Contact Features	
Contact Layout	Matrix

Housing Features	
Connector Style	Plug
Centerline (mm [in])	6.00 [0.236]
Housing Material	Nylon - GF
Housing Color	Light Gray

Configuration Features	
Number of Positions	15

Industry Standards	
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Identification Marking	
Keying	C

Environmental	
Operating Temperature (°C [°F])	-55 – +150 [-67 – +302]
Halogen Free	Yes

Conditions for Usage	
Applies To	Wire/Cable
Glow Wire Rating	High Temperature Part - Not Glow Wire

Operation/Application	
Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Power

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling