



PRODUCTS

Chilisin provides inductor turnkey solutions for EMI, power and RF and a global technical team to support its customers. Chilisin has become one of the few inductor suppliers capable of providing a complete "one-stop shopping" experience.



Products Line

- Power Inductor
- Chip Inductor
- Bead
- Common Mode Choke

Product Search

Submit

LVS404018

Home > Products > Power Inductor > LVS404018

Part Number : LVS404018-101?-N

Structure	Closed Magnetic Circuit Type - Automatic Assembly
Inductance(?H)	100
Tolerance(±%)	20,30
Test Frequency	100kHz,1V
RDC(ohm)	1.5
RDC Tolerance(±%)	20
Isat(A)Typ	0.46
Isat(A)Max	0.41
Irms(A)Typ	0.38
Irms(A)Max	0.34
Operating Temperature	－ 5 5℃～ 1 2 5℃(Including self - temperature rise)
L(mm)	4.0±0.2
W(mm)	4.0±0.2
T(mm)	1.5~1.8

- 1.Isat for Inductance drop 30% from its value without current.
- 2.Irms for a 40℃ rise above 25℃ ambient.

P/N	LVS404018-101M-N
Part Numbering	
Dimensions	
Packing	
Recommended Pattern	
Electrical Characteristics Curve	

Back

