





**Part Number :** [511120210](#)  
**Product Description :** 2.50mm Pitch Wire-to-Wire Plug Housing, with Optional Panel Mount, 2 Circuits  
**Series Number :** 51112  
**Status :** New Business Not Supported  
**Product Category :** Connector Housings



## Documents & Resources

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

### Part Details

#### General

Status	New Business Not Supported
Category	Connector Housings
Series	51112
Description	2.50mm Pitch Wire-to-Wire Plug Housing, with Optional Panel Mount, 2 Circuits
Application	Signal, Wire-to-Wire
Product Name	N/A
UPC	800754314862

## Agency

CSA	LR19980
UL	E29179

## Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	885.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

This document was generated on Mar 08, 2025