

Product data sheet

Specifications

24' CABLE EXTENDER 5-WIRE #10 AWG, UL WITH L21-20R/P



PDW24L21-20XC

Overview

Lead time Usually Ships within 2 Weeks

Main

Main Input Voltage 208 V 3 phases

Main Output Voltage 120 V
208 V 3 phases

Input Connection Type NEMA L21-20P

Number of cables 1

Provided equipment Installation guide

Physical

Colour Black

Height 6.4 cm

Width 5.1 cm

Depth 731.5 cm

Net weight 3.45 kg

Mounting location Front

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Permissible voltage 200...240 V

Max line current 20 A

Output

Max current draw 20 A

Conformance

Product certifications UL listed

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	44.5 cm
Package 1 Length	30.5 cm
Package 1 Weight	3.77 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)