

Part Number : [1300360005](#)

Product Description : Mini-Change Side Mount, 5 Pole, 4 Port with Pass Thru

Series Number : 130036

Status : Active

Product Category : Passive Distribution Boxes

Engineering Part Number : DN4000




Documents and Resources

Drawings

[1300360005 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Arsenic acid (H3AsO4), triethyl ester; Dibutylphthalate; 2,4-Dinitrotoluene; Tris(2-chloroethyl) phosphate; Tetraboron disodium heptaoxide, hydrate; Trichloroethylene; 1-Methyl-2-pyrrolidone... per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	130036
Description	Mini-Change Side Mount, 5 Pole, 4 Port with Pass Thru
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
UPC	78678869022

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	7.0A
Functional Wiring	PNP
Voltage - Maximum	120V AC/DC
Wiring Configuration	Passive Drop

Physical

Bus I/O	Mini-Change
Cable Connector Orientation	N/A

Cable Length	N/A
Home Run Cable Length	N/A
Home Run Connector	N/A
Home Run Interface	N/A
Keyway	Single
LED Indicator	None
Material - Cable Jacket	N/A
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	391.450/g
Orientation	Side Mount
Poles	5
Poles (wired)	4
Ports	4
Temperature Range - Operating	0° to +60°C

This document was generated on Apr 28, 2026