



PRODUCT SELECTOR

PRODUCT TYPE	POSITIONS	IP RATING	AMPERAGE	HOUSING MATERIAL	PRODUCT LINE	SERIES
Search All ▼	Search All ▼	Search All ▼	Search All ▼	Search All ▼	Search All ▼	Search All ▼
SEARCH						
RESET						

OUR PRODUCT LINES

- A SERIES
- C091 CONNECTORS
- C16 CONNECTORS
- C700 SERIES SMART CARD
- DISTRIBUTED POWER & CONTROL / FACTORY AUTOMATION
- ECOMATE
- HEAVYMATE CONNECTORS
- M SERIES
- MOTION CONTROL
- RADSOK
- 44 SERIES CIRCULAR
- MOLDED CABLE ASSEMBLIES
- DISTRIBUTORS
- ONLINE CATALOGS

HAVE A QUESTION?

Live Chat is Available



Home > Heavymate Connectors > Heavymate F > Pin Modules

## C14610A00450015 Pin module for turned contacts, 4.

PART NUMBER C14610A00450015



**DESCRIPTION**

Pin module for turned contacts. May be engaged or disengaged when live but without electrical load. If this connector is mated or unmated under load, the load shall be reduced to 10% of rated current. High profile housings/hoods are recommended.

**SPECIFICATIONS**

- Contacts: 4
- Color: Black
- Contact Material: CuZn (brass)
- Contact Plating: Silver
- Contact Resistance: ≤ 5 m ohms
- Insert Material: PA 6.6
- Insertion/Withdrawal Force: 30-40 N
- Insulation Resistance: > 10(10) ohms
- Lifetime: > 500 mating cycles
- Operating Temperature: -40°C to +125°C
- Protection: IP00 unmated, IP2 mated
- Rated Impulse Voltage: 8000V
- Rated Voltage: 830V
- Termination: Crimp
- Type: Pin
- Version: Turned crimp contact
- Wire Gauge: 1.5 - 6.0mm² (16-10 AWG)

QUANTITY  [REQUEST A QUOTE](#)

Related Items

 <p>C14610A00490115 Shielded pin module for turned contacts, 4.</p> <p><a href="#">REQUEST A QUOTE</a></p>	 <p>C146A05100G8 Pneumatic pin module for bus signals.</p> <p><a href="#">REQUEST A QUOTE</a></p>	 <p>C146D04001E8 Pin module for stamped 2.5mm contacts. (4+PE)</p> <p><a href="#">REQUEST A QUOTE</a></p>	 <p>C146D05001E8 Pin module for stamped 2.5mm contacts.</p> <p><a href="#">REQUEST A QUOTE</a></p>
---	---	--	---