



Color: yellow Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	3,000 labels/reel; 2 lines
Printing device	Smart Printer (thermal transfer printer)

Physical data

Depth	0.26 mm
Marking surface	7 x 20 mm

Mechanical data

Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	yellow
Material	Plastic-coated cotton fabric
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Natural rubber
Halogen-free	Yes
Weight	187 g
Fire load	0 MJ



Environmental requirements	
Ambient temperature (storage)	+10 ... +21 °C
Ambient temperature (operation)	+180 °C
Relative humidity	40 ... 50 %

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821674894
Customs tariff number	58071090000

Product classification	
UNSPSC	55121612
eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 8.0	EC001288
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 210-811/000-002	

Documentation	
Operating Instructions	
210-811 Handha- bungshinweis zum Druckmaterial	<div><div>1</div><div>28.08.2020</div><div>pdf 1397.18 KB</div><div></div></div>

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com