

SEK-18 ACC.STRAIN RELIEF CLAMP FE 40P




Image is for illustration purposes only. Please refer to product description.

Part number	09 18 540 9002
Specification	SEK-18 ACC.STRAIN RELIEF CLAMP FE 40P
HARTING eCatalogue	https://b2b.harting.com/09185409002

Identification

Category	Accessories
Series	SEK
Type of accessory	Strain relief clamp

Version

Size	40 poles
------	----------

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	100
Net weight	1.296 g
Country of origin	Romania



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85389099
GTIN	5713140033726
ETIM	EC002943
eCl@ss	27440292 Connector component (accessories)