

Data Sheet | Item Number: 247-524

Mini-WSB marking card; as card; MARKED; 50 ... 99 (2x); not stretchable; Horizontal marking; snap-on type; white

<https://www.wago.com/247-524>



Color: white

Similar to illustration

Technical data		
Suitable		for WAGO I/O System
Marking method		Thermal transfer
Marking		50 ... 99
Marking (number)		2
Marking direction		Horizontal marking
Marking color		black
Marking type		Numbers
Marking layout		Consecutive numbers per strip
Delivery form		Marker card
Delivery form configuration		10 strips with 10 markers per card

Physical data	
Height	152 mm / 5.984 inches
Width	56.8 mm / 2.236 inches
Depth	3.2 mm / 0.126 inches
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	6.2 g
Fire load	0.185 MJ



Commercial data		
Product Group	2 (Terminal Block Accessories)	
PU (SPU)	50 (5) pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4017332253505	
Customs tariff number	49119900000	

Product Classification		
UNSPSC	39131505	
eCl@ss 10.0	27-14-11-37	
eCl@ss 9.0	27-14-11-37	
ETIM 9.0	EC000761	
ETIM 8.0	EC000761	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant,No Exemption	

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 247-524

↓

Installation Notes

Marking



Marking via Mini-WSB Quick Marking System.