

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1110150301](#)
Status: **Active**
Overview: [HSAutoLink Interconnect Systems](#)
Description: HSAutoLink Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 1.50m Length, Polarization B

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-68800-001-001 \(PDF\)](#)
[Datasheet \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable Assemblies
Series [111015](#)
Application Automotive
Assembly Configuration Dual Ended Connectors
Comments USCAR-30 Compliant
Connector to Connector USB Type A-to-Mini-B
Overview [HSAutoLink Interconnect Systems](#)
Product Name HSAutoLink USCAR/USB
UPC 883906510114

Physical
Cable Length 1.50m
Circuits (Loaded) N/A
Gender Male-Female
Lock to Mating Part Yes
Net Weight 75.400/g
Number of Rows 1
Single Ended No
Wire/Cable Type Round

Material Info

Reference - Drawing Numbers

Product Specification PS-68800-001-001
Sales Drawing SD-111015-006-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Not Low-Halogen	China RoHS Green Image Not Relevant Not Contained
---	---

For more information, please visit [Contact US](#)

Search Parts in this Series
[111015](#) Series

Mates With
[49616](#) USCAR/USB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION