


[→ Honeywell.com](#) [→ Automation & Control Solutions](#)
[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

Honeywell Sensing and Control

Search

**2450RC 00820401**

(Home : Products : Sensors » Thermostats » 2450RC)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

Technology

- Electromechanical (9307)
- Magnetic (541)
- Microstructure (1495)
- Optical/Infrared (1042)
- Thick Film (1409)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

Wireless Switches Offer
Unlimited Benefit
Basic Switches Are Not Created
Equal
Applying Precision Switches
Sensors for Medical Devices
New Ways to Measure Torque
Choosing Safety Switches
Specifying Hour Meters

Need help?

[Click here to contact us](#)

2450RC Series Ceramic Automatic Reset Thermostats

*Actual product appearance
may vary.*

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	15 A/10 A
Voltage	120 Vac/250 Vac
Operating Temperature	0 °C to 260 °C [32 °F to 500 °F]
Environmental Exposure Range	-20 °C to 287 °C [0 °F to 550 °F]
Open Temperature	171.1 °C [340 °F]
Close Temperature	143.3 °C [290 °F]
Open Tolerance	8.3 °C [15 °F]
Close Tolerance	11.1 °C [20 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Ceramic
Contact Material	Silver/nickel alloy
Agency Approvals and Standards	UL, CSA, VDE
Mounting	B201 Fixed bracket
Series Name	2450RC

contacts

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

[Login to iCOM](#)
[Login to Rep/AD Portal](#)
[Login to Digital University](#)

News Center

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

MICRO SWITCH
Anniversary site

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)