



PRODUCTS

Chilisin provides inductor turnkey solutions for EMI, power and RF and a global technical team to support its customers. Chilisin has become one of the few inductor suppliers capable of providing a complete "one-stop shopping" experience.



- Power Inductor
- Chip Inductor
- Bead
- Common Mode Choke

Product Search

Submit

CUW31

Home > Products > Common Mode Choke > CUW31



Part Number : CUW31T-222M-N

Size Code(JIS/EIA)	3216/1206
Impedance(?)	2200
Tolerance(±%)	20
Test Frequency(MHz)	100
RDC(?)Max	1.2
IDC(mA)	200
Insulation Resistance (M?)	10
Rated Voltage(Vdc)	50
Operating Temperature	－4 0℃～1 0 5℃(Including self - temperature rise)
L(mm)	3.20±0.20
W(mm)	1.60±0.20
T(mm)	1.90±0.20

- 1.RDC: SINGLE WIRE TEST VALUE
- 2.IDC for Inductance drop 10% from its value without current.

P/N	CUW31T-222M-N
Part Numbering	
Dimensions	
Packing	
Recommended Pattern	
Electrical Characteristics Curve	

Back

