

Electronic housing - HCS-T MICRO X 2AA 1 1 7035 - 2203128

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Handheld housing, T-Micro, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, closed with keypad slot, battery compartment cover and battery contacts for 2 AA batteries

Why buy this product

- ✓ Item is from the HCS product range
- ✓ Suitable for handheld devices
- ✓ Ergonomic straight or staggered housing design
- ✓ Integration of LCD displays and membrane keypads
- ✓ Degree of protection: up to IP54
- ✓ Temperature range: -20 °C to +50 °C
- ✓ Shock-resistant ABS plastic
- ✓ Flammability rating UL 94-V0

RoHS

Key Commercial Data

Packing unit	1
GTIN	 4 055626 356464
GTIN	4055626356464
Custom tariff number	39269097

Technical data

General

Housing type	Complete housing
Housing material	ABS
Color	light gray

Dimensions

Electronic housing - HCS-T MICRO X 2AA 1 1 7035 - 2203128

Technical data

Dimensions

Length	110 mm
Constructional height	26 mm
Width	70.5 mm

Technical data

Flammability rating according to UL 94	V0
--	----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 5.1	27180506
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
----------	----------