C2G

# 5ft (1.5m) Cat6 Snagless Unshielded (UTP) Slim Ethernet Network Patch Cable - White

Part No. 01187



The Cat6 Snagless Unshielded (UTP) Slim Network Patch Cable is the perfect solution for high density datacenter applications. The use of 28 AWG conductors allows for a 36% reduction in diameter over a standard Cat6 network patch cable. This reduced diameter provides a smaller cable surface area which allows for increased airflow when compared to standard Cat6 cables. The 28 AWG conductors also allow this cable to have a smaller bend radius than standard Cat6 cables. The small size and small bend radius of this cable allows it to be easily routed through cable management panels.
This cable is designed for fast Ethernet networks that require bandwidth-intensive voice, data, or video distribution applications. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

- This patch cable does not meet the recommend conductor size, 22-26AWG, requirement of ANSI/TIA-568-C.2. Attenuation is increased due to the smaller 28AWG conductors.

Maximum cable length recommendations:

- 96 Meter Channel (90 meters of horizontal cable and up to 6 meters of slim network patch cables)
- 93 Meter Channel (83 meters of horizontal cable and up to 10 meters of slim network patch cables)
- For POE/POE+ applications we limit bundles to 40 cables due to heat dissipation of these reduced diameter cables.

## Features & Benefits

36% reduction in diameter compared to standard Cat5e cables

Snagless connector design

Meets the ANSI/TIA-568-C.2 standard for Patch Cord Performance

28AWG construction

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | C2G | Color | White |
| UPC Number | 757120011873 | Country Of Origin | Vietnam |
| Features | PoE (Power Over Ethernet) | Application Sector | Commercial, Industrial, Residential |
| Warranty Type | Lifetime | Type | Cable |

### Dimensions

| | | | |
|---|---|---|---|
| Product Length US | 5.0 FT | Cable Length | 5 ft |



Downloaded from Arrow.com.

| | |
|---|---|
| Outside Diameter | 3.8 mm |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| CE Certified | Yes | REACH Compliant | Yes |

## Additional Information

| | |
|---|---|
| RoHS Compliant | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Jacket Material | PVC (Polyvinyl Chloride) | Category Performance Application | Cat6 |
| Wiring Scheme | T568B | Wire Gauge | 28 AWG |
| Shielded/Unshielded Cable | Unshielded | Conductor | 4-Pair Twisted |
| Shield Type | UTP | Cable Type | Ethernet Patch Cable |
| Jacket Rating | Standard / Non-Rated | Cable Diameter | 3.8 mm |
| Connector Type | Booted, Slim, Snagless | Indoor/Outdoor | Indoor |
| Connector 2 | RJ-45 Male | Connector 1 | RJ-45 Male |
| Bandwidth | 500 mHz | Storage Temperature | -20° - 80° C |



Downloaded from Arrow.com.