



**Part Number :** [1301540048](#)

**Product Description :** Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V

**Series Number :** 130154

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 14W47-Y



---

## Documents and Resources

### Drawings

[1301540048 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | Not Reviewed per SJ/T 11365-2006               |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                |
| REACH SVHC         | Not Reviewed per D(2025)4165-DC (25 June 2025) |
| EU RoHS            | Not Reviewed per EU 2015/863                   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|                    |  |
|--------------------|--|
| Status             | Active   |
| Category           | Wiring Devices   |
| Series             | 130154   |
| Description        | Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V |
| IP Rating          | IP67   |
| NEMA Configuration | NEMA 5-15  |
| Product Name       | Watertite Extreme  |
| Specialty          | N/A  |
| Type               | Molded Y Cordset   |
| UPC                | 78678801400  |

#### Agency

|     |         |
|-----|---------|
| CSA | LL52750 |
| UL  | E38085  |

#### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 15.0A |
| GFCI                          | No    |
| Voltage - Maximum             | 125V  |

#### Physical

|                     |             |
|---------------------|-------------|
| Cord Grip Body Size | F2 1/2"     |
| Cord Type           | 12/3 SOOW   |
| Flange              | No          |
| Flip Lid            | No          |
| Gender              | Male-Female |

|                   |               |
|-------------------|---------------|
| Length            | 0.91m (3.0')  |
| Lighted Connector | No            |
| Locking Blade     | No            |
| Net Weight        | 1023.757/g    |
| Poles             | 2-pole/3-wire |
| Receptacle Type   | Duplex        |

---

This document was generated on Dec 30, 2025