



Part Number : [1301430245](#)
Product Description : Watertite Extreme Cordset,
12 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length
7.62m (25.0'), NEMA L16-20, 3ø 480V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 26W76A124



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Watertite Extreme Cordset, 12 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L16-20, 3Ø 480V
IP Rating	IP67
NEMA Configuration	NEMA L16-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678871266

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	3Ø 480V

Physical

Cord Grip Body Size	F3 3/4"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No

Locking Blade	Yes
Net Weight	126.000/kg
Poles	3-pole/4-wire
Receptacle Type	Single

This document was generated on May 27, 2026