

3-Port USB 3.x (5Gbps) Hub with LAN Port, USB-C to 3x USB-A Ports and Gigabit Ethernet, Black

MODEL NUMBER: **U460-003-3A1GB**



Adds 3 USB-A ports and a Gigabit Ethernet port to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-003-3A1GB USB 3.1 Gen 1 USB-C Portable Hub/Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, charging a mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

The plug-and-play U460-003-3A1GB requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Three USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer. Each port provides up to 5V/1.5A (7.5W) for fast charging of mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Features

Turn Your Device's USB-C Port into a Workstation

- Ideal for adding USB peripherals, powering a mobile device, and connecting to a Gigabit Ethernet network simultaneously
- Plug-and-play operation with no software, drivers or external power required
- White LED indicates unit is connected and receiving power
- Lightweight aluminum housing about the size of a credit card for easy carrying in a backpack or laptop bag

Connect USB Peripherals

- 3 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals
- Supports up to 5V/1.5A (7.5W) for fast charging of mobile devices
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1

Note: Host must support USB OTG (On-the-Go)

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 1.5A each for charging devices
- Supports true 10/100/1000 Mbps Ethernet network speeds
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

Package Includes

- U460-003-3A1GB USB 3.1 Gen 1 USB-C Portable Hub/Adapter, Black
- Quick Start Guide

Access a Wired Gigabit Ethernet Network

- RJ45 port supports true 10/100/1000 Mbps network speeds
- Recommended for a faster wired network connection or getting online when no Wi-Fi is available

Built-In Cable with Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Manufactured to Exacting Specifications

- Compliant with IEEE 802.3az (Energy Efficient Ethernet)
- Supports IPv4 and IPv6 pack COE (Checksum Offload Engine) to reduce CPU loading
- Supports full- and half-duplex operations
- Supports Wake-on-LAN, jumbo frames and VLAN tagging

Specifications

OVERVIEW	
UPC Code	037332209597
Product Type	Hub
Technology	Cat5/5e; Cat6; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	12
Product Length (cm.)	30.48
Product Length (ft.)	1
Product Length (m)	0.3
BATTERY	
Battery Charging (5V/1.5A Port)	Yes

POWER	
Power Consumption (Watts)	0.95
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White LED indicates power
CHARGING	
Total Charging Watts	7.5
Charging Ports	USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	(3) 1.5A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	1.06 x 5.71 x 2.95
Shipping Weight (lbs.)	0.18
Unit Dimensions (hwd / in.)	0.840 x 3.800 x 1.200
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	3.2 BTU/Hr
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3u; 802.3ab; 802.3az
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)

Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Driver Required	No
Recommended Category Cable	N201-Series Cat6 Gigabit Snagless Patch Cables
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty