







Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
 Verpackungseinheit: 280 Stück
packaging unit: 280 pcs



Abspulrichtung - *reel off direction*



Anforderungsstufe 1
performance level 1


Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinnt 4-6 μm
terminal area 4-6 μm tin plating

Koplanarität der Anschlüsse $\leq 0,1 \text{ mm}$
coplanarity area of termination $\leq 0,1 \text{ mm}$

BA 7-03 - Standard Bauhöhe


type 7-03 - standard assembly height



Leiterplatten-Layout Vorschlag für SMT
PCB-Layout Proposal for SMT

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmackschutzverletzung vorbehalten.

*The german version of this drawing has been offered for convenience only and may deviate from the english original.
In case of any deviation the English version shall prevail.*

Dimension no.				Tolerances				Scale 5:1			
				ISO 8015		All Dimensions in mm		Material			
<u>Customer drawing:</u> This Drawing is a controlled Document.				Subject to modification without prior notice. Drawing will not be updated.				Federl. SMC-B 20-SMD-BA7-03 Female SMC-B 20-SMD-type7-03			
c1				12.05.2023				C-354063-E			
Index				Date							
								A3			
 TE Connectivity								Class SMCB			