



**Part Number :** 02092118

**Series Number :** 1380

**Product Category :** Crimp Terminals

**Packaging Alternative :** 02092116 (Reel)

**Product Description :** 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag

**Status :** Active


**Engineering Number :** 1380-(P901)L

Documents & Resources

- Drawings**
- [Drawing 002092118\\_sd.pdf](#)
  - [Packaging Design Drawing PK-1190-003-001.pdf](#)
- Specifications**
- [Product Specification PS-02-09-001.pdf](#)
  - [Test Summary 11890000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	1380
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag
Application	Power, Wire-to-Wire
Product Family	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
UPC	800753746114

### Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.206/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	N/A

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Dual Row Connector Housings	<u>1261</u>
Standard .093" Pin and Socket 3 Row Connector Housings	<u>1292</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1396</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1490</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1545</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1619</u>

---

## Application Tooling

### Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	<u>11020003</u>
Extraction Tool for Standard .093" Pin and Socket Terminals	<u>11030006</u>
Extractor Tool for .093 and HCS-125 Product Series	<u>638240200</u>
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 18 AWG	<u>638280900</u>
Hand Crimp Tool for .093" Pin and Socket Crimp Terminals, 22 AWG	<u>638281400</u>
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 20 AWG	<u>638281700</u>

---

This document was generated on May 11, 2024