



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Ratchet Configuration: **Not Releasable, Not Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Electric, Manual
Tooling Type	Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC







Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 131184 BNC PLUG ASSY	 TE Part # 131197 COAX TNC PANEL JACK ASSY	 TE Part # 131232-1 TNC E TYPE PLUG ASSY	 TE Part # 213841-8 PWRBAND PIN CNT ASSY,8-10,L.P.
 TE Part # 58380-2 AMP MNL 10 DIE SET	 TE Part # 213843-4 PWRBAND SKT CNT ASSY,8-10,L.P.	 TE Part # 2-66740-1 TYPE XII FEMALE CONT (LP)	 TE Part # 213841-4 PWRBAND PIN CNT ASSY,8-10,L.P.
 TE Part # 213847-3 POWERBAND CONT ASSY,SILVER PLT	 TE Part # 66740-2 TYPE XII FEMALE CONT (L.P.)	 TE Part # 66740-8 TYPE XII FEMALE CONT (L.P.)	 TE Part # 69732 PIDG STRATO 22-20 DIE SET





TE Part # 90348-2
HIGH CURRENT HERMAPHRODITIC 8
DIE SET



TE Part # 131223-1
COAXICON BNC PLUG ASSY




TE Part # 2-55825-1
16-14 PRE-INSUL SEALED SPLICE



TE Part # 213845-3
POWERBAND CONT ASSY,SILVER PLT



TE Part # 213841-3
POWERBAND CONT ASSY,SILVER PLT



TE Part # 213843-3
POWERBAND CONT ASSY,SILVER PLT



TE Part # 66741-6
TYPE XII FEMALE CONT (L.P.)




TE Part # 69735
PIDG STRATO 12-10 DIE SET


Customers Also Bought




TE Part #810033-000
2019D0309-0



TE Part #988596-000
AE-205



TE Part #9101754001
CGPT-3.2/1.6-45-SP



TE Part #90145-2
TYPE XII MALE FEMALE ASSY 16-14
DIE SET



TE Part #500024-1
SPIRAP 1/4" PTFE, NAT, 50 FT



TE Part #696683-1
AMPOWER,500MCM,2-1/2,1.25 CNTR




TE Part #1901600-2
CCII PIDG STRATO 18-16 ASSY



TE Part #1901611-2
CCII PIDG STRATO 24-20 ASSY



TE Part #3-2176408-3
3560 120K 5%



TE Part #1-2186559-1
1966-RIBBON-NAR

Documents



Product Drawings

C-HEAD FRAME W/O DIES

English

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English