


APPROVED: _____


DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	9/20/10	
A		REVISED SPEC.	12/10/12	
B		UPDATED DIM.	3/16/15	HR/AY
C		UPDATED SPEC.	4/7/15	AY/GC
D		UPDATED DIM.	12/1/16	HR/MC











Postitions: 4 thru 60
A = .020 [0.50] x No. of Spaces
B = .020 [0.50] x No. of Positions + .024 [0.60]
C = .020 [0.50] x No. of Positions + .181 [4.60]
D = .020 [0.50] x No. of Positions + .220 [5.60]
E = .207 [5.25].....4 thru 34
.226 [5.75].....35 thru 60

SPECIFICATIONS:
Material:
Insulator: Hi-temp thermoplastic, rated UL 94V-0, White
Latch: Hi-temp thermoplastic, rated UL 94V-0, Black
Contact: Phosphor Brzone
Fitting Nail: Copper Alloy, Tin plated
Plating:
Tin over Copper underplate overall.
Electrical:
Operating voltage: 50 VAC/DC
Current rating: 0.4 A AC/DC
Contact resistance: 30 mohms Max.
Insulation resistance: 500 mohms Min.
Withstand Voltage: 250V AC/minute
Temperature Rating:
Operating temperature: -45°C to +85°C
Environmetal:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	DY	9/20/10
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: ZIF FLEX CIRCUIT CONNECTOR
SIDE ENTRY, SMT TYPE

SIZE	PART NO.	REV.
X	PCA-6K-XX-HX-3	D

REF: S00167T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.