





DB UNLIMITED

Part Number:	DRAWN	12/20/2017
	CJ	
	CHECKED	12/20/2017
Description:	P.D.	12/20/2017
	APPROVED	
	C.E.	12/20/2017
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Sound Pressure Level	97	dB (@ 10cm)				
Resonant Frequency	400	Hz				
Frequency Range	400 ~ 5,000	Hz				
Nominal Power	0.25	W				
Max. Power	0.5	W				
Impedance	32	Ω				
Cone Material	Paper					
Mount Type	Flush Mount					
Storage Temperature	-25 ~ +55	°C				
Operating Temperature	-25 ~ +55	°C				
Weight	46	g				

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	10/21/2013	J.S.
1	Updated to new template, Corrected SPL	12/20/2017	C.E.

NOTES	
1) All dimensions are in mm unless otherwise noted	
2) All tolerances are ± 0.5 mm unless otherwise noted	
3) All parts meet RoHS	
4) Subject to change or redrawn without notice	