

32-Port USB Charging Station with Syncing, 5V 80A (400W) USB Charger Output, 2U Rack-Mount

MODEL NUMBER: **U280-032-RM**



2U rack-mountable USB charger with integrated hub charges and syncs up to 32 tablets, smartphones and other mobile devices. Recommended for schools, offices and other environments where multiple USB devices are used.

Features

Charges Up to 32 Tablets, Smartphones and Other USB Devices

- Recommended for schools, offices and other environments where multiple USB devices are used
- Compatible devices include iPad, iPod, iPhone and Android tablets and smartphones
- Provides up to 5V, 2.4A (12W) of charging power to each port
- LED indicators signal ports in use
- Backward compatible with previous USB generations
- Supports data transfer rates up to 480 Mbps

Also Syncs Devices via Connected Computer

- Syncs USB devices using its compatible software, such as iTunes or Apple Configurator
- Included USB cable connects USB-B port and computer's USB-A port

Mini-USB Firmware Port

- Enables future software upgrades to support newer devices

Easy Installation and Connection

- Mounts in 2U of EIA-standard 19 in. rack using included hardware
- Also installs on level surface using included rubber feet
- Conveniently configures for professional, educational or personal installation
- 10-ft. (3.05 m) NEMA 5-15P to C13 power cord included

Highlights

- Maximum charge output of 2.4A per USB port
- Supports USB 2.0 data transfer rates up to 480 Mbps
- Syncs any USB device using its compatible software
- Enables future software upgrades to support newer devices
- Mounts in 2U of EIA-standard 19 in. rack

System Requirements

- Tablet, smartphone or other smart device with USB port
- Computer with available USB port (if syncing)

Package Includes

- U280-032-RM 32-Port USB Charging Station
- NEMA 5-15P to C13 power cord, 10 ft.
- USB 2.0 A/B cable, 6 ft.
- (4) Rubber mounting feet
- Mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Durable steel housing

TAA-Compliant

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332193520
Product Type	Multi-Device Charger
Charging Form Factor	Rack Mount
Functions	Charge; Sync
Device Compatibility	Tablet; Phone
Technology	USB; USB 2.0 (High Speed)
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Connection Type	IEC320-C14
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz
Input Plug Type	C14
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Current	8A
OUTPUT	
Output Capacity	5V 80A (400W)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (32x USB Charging, 1x Sync)
CHARGING	
Number of Charging Ports	32
Total Charging Amps	80A
Total Charging Watts	400
Charging Method	USB



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	19.56 x 42.67 x 49.78
Shipping Dimensions (hwd / in.)	7.70 x 16.80 x 19.60
Shipping Weight (kg)	8.26
Shipping Weight (lbs.)	18.20
Unit Dimensions (hwd / in.)	3.4 x 17.3 x 11.9
Unit Dimensions (hwd / mm)	86.7 x 440 x 301.7
Unit Packaging Type	Box
Unit Weight (kg)	5.94
Unit Weight (lbs.)	13.1
Number of Shelves	0
ENVIRONMENTAL	
Operating Temperature Range	32 to 95 F (0 to 35 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	5% to 95% RH, Non-Condensing
AC Mode Efficiency Rating (100% Load)	74.57
BTUs	382.2 BTU/Hr (Full load)
Power Consumption (Watts)	112
CONNECTIONS	
Ports	32
Side A - Connector 1	(32) USB A (FEMALE)
Side A - Connector 2	USB B (FEMALE)
Side A - Connector 3	(2) MICRO-USB B (FEMALE)
Side B - Connector 1	IEC-320-C14



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FEATURES & SPECIFICATIONS	
Driver Required	No
SPECIAL FEATURES	
Cord Management	No
EMI/RFI Line Noise Protection	Yes
Locking	No
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1: 2007, CAN/CSA-C22.2 No. 60950-1:07, IEC 60950, FCC & IEC Class B, NOM, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>