

C-22

BURNDY® PRODUCTS

C-22

C-22 : GRD CL BARE 1-1/4-2\



ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)
[✉ Email Datasheet](#)
[🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)
[📄 > Sample request](#)
[€ > Price request](#)

Specifications

[Download document](#)

General	Dimensional	Physical	Approvals / Certifications	Other Features
General				
Armored Cable			No	
Dimensional				
Pipe Size			1-1/4 in. 1-3/8 in. 1-3/4 in. 1-1/2 in. 1-7/8 in. 1-5/8 in. 2 in.	
Pipe Size (Range)			1-1/4 in. to 2 in.	
Physical				
Material/Body			Cast Bronze	
Type of Hardware			Zinc Plated	
Conductor Size (Range)			10 Stranded to 2 Stranded	
Ground Strap			No	
Approvals / Certifications				
UL Listed			Yes	
CSA Certified			Yes	
Other Features				
UPC			78181014231	
Keyword			groundclamps	