



REV.	DATE	ECR NO.	DESCRIPTION
NC	10/25/10	XXXXXX	INITIAL RELEASE





TOP VIEW

RECOMMENDED PCB LAYOUT



BOTTOM VIEW



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex				
					DRAWN	M.ZHANG		10/25/10					
					CHECKED				PART DESCRIPTION SMA END LAUNCH RECEPT. JACK (.032” BOARD THICKNESS)				
					ISSUED								
SHEET		1 OF 1				PART NO. 132415							
CAD FILE		C:/CONNEX/132415.DWG		DWG. NO.		132415.DWG		REV.	NC	SIZE	A	SCALE	NA

SMA END LAUNCH RECEPT. JACK
(.032" BOARD THICKNESS)

132415

DWG. NO. 132415.DWG

REV. NC

SIZE A

SCALE NA