

Specifications

Eaton DR1030-151-R



Eaton DR1030 inductor, 150 μ H, 0.68 A Irms, 0.86 A ISAT, 700 m Ω resistance, SMT mounting, Ferrite, 2-pins, 1000 qty.

Photo is representative



General specifications

PRODUCT NAME	Eaton DR1030 inductor
CATALOG NUMBER	DR1030-151-R
UPC	051712825153
PRODUCT LENGTH/DEPTH	10.5 mm
PRODUCT HEIGHT	3 mm
PRODUCT WIDTH	10.3 mm
PRODUCT WEIGHT	1.2 g
COMPLIANCES	RoHS Compliant

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.68 A
ISAT	0.86 A
PACKAGE QUANTITY	1000
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	700 mΩ
TERMINALS	10.0x10.0x3.0mm
SERIES	DR1030

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
DR1030-151-R](#)

[Eaton DR1030 shielded
power inductors data
sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

