

**Part Number :** [1300980027](#)

**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 3.18-4.75mm (.125-.187")

**Series Number :** 130098

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 5500



---

## Documents and Resources


### Drawings

[1300980027 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 3.18-4.75mm (.125-.187")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872110

### Agency

CSA	LR32159
UL	E76954

### Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	3.18-4.75mm (.125-.187")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	32.498/g
Number of Holes	1

O-Ring	No
Thread Size	3/8" NPT

## Mates With / Use With

### Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/8" NPT	<u>1300990142</u>
MAX-LOC Gasket Sealing Ring, 3/8" NPT, Black	<u>1300990148</u>

---

This document was generated on Apr 11, 2026