

## Specification Sheet

Part Number: 151-00993

The 90-degree configuration of this mini channel creates a solution for routing a wire harness around a corner.

Design allows the mini channel to be used with a wide range of panel thicknesses and hole diameters.



Disc prevents rattling in high-vibration applications and protects against leakage and debris.

Mini Channel, 1.38" Long, 90° Angle, Fir Tree FT6, PA66HIRHSUV, Black, 4000/pkg

Article Number 151-00993

Type BC90FT6

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Bundling Clips create a solution that allows the harness to be routed around a corner and fixated into the panel at this location.

Short Description Mini Channel, 1.38" Long, 90° Angle, Fir Tree FT6, PA66HIRHSUV, Black, 4000/pkg

Global Part Name BC90FT6-PA66HIRHSUV-BK

Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	Fir Tree
Width W (Imperial)	0.06
Width W (Metric)	1.5
Height H (Imperial)	1.03
Height H (Metric)	26.2
Diameter D (Imperial)	0.84
Diameter D (Metric)	21.34
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Metric)	21.34
Disc Diameter (Imperial)	0.84
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature intermittent, 1000 hours	+320°F (+160°C)
Operating Temperature intermittent, 5000 hours	+257°F (+125°C)
Operating Temperature intermittent, 500 hours	+329°F (+165°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Privacy Policy](#)   [Cookie Policy](#)   [Terms and Conditions](#)