
**Part Number :** 152670303
**Product Description :** 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 203.00mm Cable Length, Tin (Sn) Plating, 14 Circuits
**Series Number :** 15267
**Status :** Active
**Product Category :** Flat-Flexible Cable (FFC)



## Documents and Resources

### Drawings

152670303_sd.pdf

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-15267-001-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Flat-Flexible Cable (FFC) |
| Series | 15267 |
| Description | 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 203.00mm Cable Length, Tin (Sn) Plating, 14 Circuits |
| Comments | Contacts on the same side, Type A |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 884982442658 |

### Agency

| | |
|---|---|
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 1.2A |
| Voltage - Maximum | 60V AC |

### Physical

| | |
|---|---|
| Cable Length | 203.00mm |
| Circuits (Loaded) | 14 |
| Contact Layout Type | A (same side) |
| Design Feature | Flexible |
| Flammability | 94V-0 |
| Material - Plating Mating | Tin |

Downloaded from Arrow.com.

| | |
|---|---|
| Net Weight | 2.557/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.00mm |
| Temperature Range - Operating | -40° to +105°C |
| Termination Style | FFC Connector |
| Wire/Cable Type | Flat Flexible Cable (FFC) |
| Wire Size (AWG) | N/A |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 14 Circuits, Tin-Bismuth Plating | 522711479 |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 14 Circuits, Tin-Bismuth Plating | 526101471 |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 14 Circuits, Tin-Bismuth Plating, with Pick-and-Place Tape | 526101475 |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 14 Circuits | 528081470 |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 14 Circuits | 528081471 |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 14 Circuits, Tin-Bismuth Plating | 522071485 |

Downloaded from Arrow.com.

| | |
|---|---|
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Right-Angle, Non-ZIF, Top Contact Style, 14 Circuits | 527931470 |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount Compatible, Non-ZIF, Kinked PC Tails, 14 Circuits | 528061410 |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 14 Circuits | 528071410 |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 14 Circuits | 528521470 |



Downloaded from Arrow.com.