

Product data sheet

Specifications



MGE Galaxy 3500 Maintenance Bypass Cabinet 10-30kVA 208V Floormount with 42 Pos. Distribution Panel

G35TSBP10K30F-DP

⚠ Discontinued - Service only

⚠ Discontinued on: 05 July 2021

⚠ To be end-of-service on: 31 December 2030

Overview

Lead time Usually Ships within 2 Weeks

Main

Main Input Voltage 208 V 3 phases

Main Output Voltage 208 V

Rated power in VA 30000 VA

Provided equipment Installation guide

Physical

Height 148.7 cm

Width 35.1 cm

Depth 83.7 cm

Net weight 154.55 kg

Mounting support Floor

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Network frequency 60 Hz

Conformance

Product certifications CSA

Standards CSA C22.2 No 107.1
UL 1778

Environmental

Ambient air temperature for operation 0...40 °C

Relative humidity 0...95 %

Operating altitude 0...10000 ft

Ambient air temperature for storage	0...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...9144.00 m

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	166.37 cm
Package 1 Width	110.49 cm
Package 1 Length	72.39 cm
Package 1 Weight	189 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)