

M12 Power Male Contact Crimp 2,5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9926
Specification	M12 Power Male Contact Crimp 2,5mm²
HARTING eCatalogue	https://b2b.harting.com/21011009926

Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact
Description of the contact	23.2 mm length

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	2.5 mm²
Conductor cross-section	AWG 14

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

PROFINET	Yes
----------	-----

Commercial data

Packaging size	50
Net weight	0.64 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors