



DataTraveler Exodia M USB flash drive

With moving cap in multiple colours

Kingston® DataTraveler® Exodia™ M is a USB 3.2 Gen 1 compliant storage solution for laptops, desktop PCs, monitors and other digital devices. DT Exodia M allows quick transfers and convenient storage of documents, music, videos and more. It's available in multiple stylish colour options that correspond to capacities of up to 256GB¹. Its practical design makes it an ideal on-the-go storage solution whether at work, home or school. DT Exodia M is backed by a five-year warranty, free technical support and legendary Kingston reliability.

- Moving cap design protects USB connector
- Multiple colour options by capacity
- Loop easily attaches to key rings

Specifications

Capacities ¹	64GB, 128GB, 256GB
Interface	USB Type-A
Standard/Speed ²	USB 3.2 Gen 1
Dimensions	67.4mm x 21.8mm x 11.6mm
Weight	10g
Operating temperature	0°C~60°C
Storage temperature	-20°C~85°C
Warranty	5-year warranty, free technical support
Compatible with	Windows® 11, macOS® (v. 13.7.8+), Linux (v. 4.4.x+), Chrome OS™

Part Numbers DTXM

DTXM/64GB	DTXM/128GB	DTXM/256GB
DTXM/64GB-2P		

1. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's [Flash Memory Guide](#).

2. Performance based on USB 3.2 Gen 1 standard. Speed may vary due to host and device configuration. Backwards compatible with USB 2.0.