

Data Sheet | Item Number: 248-455

Mini-WSB marking card; as card; MARKED; U 100 (10x); not stretchable; Horizontal marking; snap-on type; white

<https://www.wago.com/248-455>



Color: white

Similar to illustration

Technical data		
Marking method		Thermal transfer
Marking		U 100
Marking (number)		10
Marking direction		Horizontal marking
Marking color		black
Marking type		Symbol
Marking layout		Same symbols per strip
Delivery form		Marker card
Delivery form configuration		10 strips with 10 markers per card

Physical data	
Height	152 mm / 5.984 inches
Width	56.8 mm / 2.236 inches
Depth	3.2 mm / 0.126 inches
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004



Material data		
Color		white
UV resistance		EN 60068-2-5:2010 Procedure B
Halogen-free		Yes
Weight		6.2 g
Fire load		0.185 MJ

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		5 (5) pcs
Packaging type		Bag
Country of origin		DE
GTIN		4066966448092
Customs tariff number		49119900000

Product Classification		
UNSPSC		55121718
eCl@ss 10.0		27-14-11-37
eCl@ss 9.0		27-14-11-37
ETIM 9.0		EC000761
ETIM 10.0		EC000761
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 248-455		

Documentation				
Bid Text				
248-455	19.02.2019	xml	2.67 KB	
248-455	16.03.2018	doc	23.50 KB	

Installation Notes

Marking



Marking via Mini-WSB Quick Marking System.