


REV.	DATE	DESCRIPTION
NC	12/11/97	INITIAL RELEASE
A	01/08/07	REVISE DESCRIPTION, UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
7						DRAWN	G.R.S.	01/08/07						
6						CHECKED				PART DESCRIPTION BULKHEAD CABLE TERMINATOR (FOR RG-174/U, 316/U CABLE)				
5	FERRULE	COPPER	NICKEL	1		ISSUED								
4	HEX NUT	BRASS	NICKEL	1		SHEET	1 OF 1							
3	LOCK WASHER	BRASS	NICKEL	1		PART NO. 142207								
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	NICKEL	1	DWG. NO. 142207.DWG REV. A SIZE A SCALE NA									
	DESCRIPTION	MATERIAL	FINISH	QTY										