



Note:

- Material: Housing-polycarbonate, clear
Terminal-0.36[.014] thick phosphor bronze.
Thick gold in localized gold plate.
Area, Gold Flash over the remainder.
Over 2.54mm[.000100] thick nickel underplate.

SEC:A-A

Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length
AT-S-26-4/4/S-5	A	1,525±20(5ft)	Silver	1,525-1,535mm
AT-S-26-4/4/S-7	B	2,135±30(7ft)	Silver	2,135-2,145mm
AT-S-26-4/4/S-10	C	3,050±60(10ft)	Silver	3,050-3,060mm
AT-S-26-4/4/S-12	D	3,660±60(12ft)	Silver	3,660-3,670mm
AT-S-26-4/4/S-14	E	4,270±60(14ft)	Silver	4,270-4,280mm
AT-S-26-4/4/S-25	F	7,625±100(25ft)	Silver	7,625-7,635mm
AT-S-26-4/4/S-50	G	15,250±150(50ft)	Silver	15,250-15,260mm

P1	P2
1 BLACK	4
2 RED	3
3 GREEN	2
4 YELLOW	1

Unit: mm

RoHS
Compliant

Scale	Free						Date	Name	Title
TOLERANCE							Drawn	03.07.13	Wilson
X.	±X						Approved	03.07.13	Groll
X.X	±X								
X.XX	±X								
DIM	TOL								
X.°	±X°								
X.X°	±X°								
Angle	TOL								
Id.	Modification								

ASSMANN
components
1940 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@assmann.us

Title Modular cable - Straight 4P4C 50µm, 26AWG, Silver, 5-50 feet	
ASSMANN WSW-No. AT-S-26-4/4/S-xx	
Drawing-No.	rev00
Replace	Sheet 1/1