



Part Number : [1300980197](#)

Product Description : MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 6.35mm (.250")

Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Part Number : 5594-005

Documents and Resources

Drawings

[1300980197 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 6.35mm (.250")
Comments	Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678850412

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	6.35mm (.250")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A

Mesh Length	N/A
Net Weight	123.000/g
Number of Holes	2 or 3
O-Ring	No
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	1300990143
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	1300990149
MAX-LOC O-Ring, 1/2" NPT	1301800314

This document was generated on May 23, 2026